



| | | |
|-----------------|------------|---|
| TITLE | | NOTE: All Purewater tanks must be fully supported on a flat, level & continuous foundation providing structural support to the tank when full to maximum operating capacity. It is essential that the user refers to the conditions of installation document prior to the installation of the tank. Under no circumstances should the tank body be used to provide support to pipework and ancillary items. The tank lid is a structural part of the tank and must be in place and fitted correctly when water is contained within the tank. |
| PW7500.INS.AB.4 | | |
| DRAWN BY | DATE | |
| J. Ellison | 24/03/2023 | |
| CUSTOMER | | |
| CUSTOMER | | |

| | |
|--|--|
| DESCRIPTION: | |
| PW7500 one piece cold water storage tank c/w raised float valve housing to provide an AB Air gap | |
| A4 | |

| | |
|-------------------------------------|--|
| ALL DIMENSIONS IN MM - DO NOT SCALE | |
|-------------------------------------|--|

| DATE | VERSION | NOTES |
|------------|---------|-------------|
| 06/11/2017 | A | FIRST ISSUE |
| | | |
| | | |
| | | |
| | | |
| | | |
| | | |

| TANK SPECIFICATION : | |
|----------------------|----------------------|
| INTERNAL DIMENSIONS | 2500 x 2000 x 1500mm |
| EXTERNAL DIMENSIONS | 2692 x 2192 x 1825mm |
| NOM. CAPACITY | 7500 Litres |
| DRY WEIGHT | 380 KG |
| INSULATION THICKNESS | 25mm |
| WRAS CERT. NUMBER | 131006 |
| MATERIAL | GRP |

SCALE:1:30 SHEET 1 OF 1